

Efficiency in the office.

The Pro-Line II filing frame is the perfect solution for professional equipment of office cabinets. It combines innovative technology with highly functional design. Its comfort features offer tangible advantages regarding its usage. The results are low production costs and high customer satisfaction.

Standard colour: black
Other colours available on request




- **Schock full extension slide**
Load capacity 70 Kg (dynamic)
- **50 mm over-extension**
Easy access and tabbing of filing maps
- **70 mm self-closing device**
Safe closing function
- **Rack + pinion parallel guidance**
One single locking device is sufficient

- **Modular filing frame**
Final assembly without tools
Same assemblies for all cabinets
Premounting of filing frame possible
- **Frame detachable from the slides**
Easy disassembly and reassembly
- **Locking systems**
adaptable to modern locking systems
from Huwil, Lehmann, Ojmar ...

Triple customer benefit.

1. Easy access

The 50 mm over-extension allows for a perfect access to the rear storage space. Protrusions or handles have no negative effect on the convenience of handling. The filing maps can be comfortably removed and filed.



2. Safe closing


The 70 mm self closing device guarantees a safe and complete closing of the frame. Malfunctions and damages of the furniture are being avoided.

On request also available with additional damping system "Soft Control 2".





3. Perfect motion

The Schöck rack + pinion parallel guidance ensures a synchronized movement. The guides run smoothly without jamming or racking even when closing the drawer from the corner.




Schock ball bearing slide with rack + pinion parallel guidance.




High load capacity

Load rate 70 Kg
LGA-tested with
100.000 cycles



Maintenance-free

Dirt will be auto-
matically displaced
by the balls



Long life durability


Lateral impacts
will be absorbed
elastically

(A) 50 mm over-extension

Easy access and tabbing of filing maps.
Telescopic extended rack.
No additional space required.

(B) 70 mm self-closing device

Safe closing function.
Integrated in the rack of the parallel guidance.
No loss of load capacity (e.g. for 3 x A4 width).



(C) Rack + Pinion parallel guidance "Synchro"


Double cog rows with involute toothing.
Blocking force is similar to a locking system.
One single locking device is sufficient.

Final assembly without tools.

The cabinet brackets are screwed into the side walls before the final cabinet assembly. At the end of the production, the filing frame will be mounted without tools. This modular system provides a high flexibility in production as well as considerably low storage costs.



Assembly:



(1) Screw-in the cabinet brackets


Hole patterns see page 6-9



(2) Attach the slide modules

Front cutout of cabinet brackets for installation with front cover.


Rear cutout for installation behind doors (see page 8-9)



(3) Attach the front and rear panel

(4) Insert the connection rod

Push both pinion retainer clips (left and right) towards the pinion wheels until they click into place



Order data for basic equipment see page 18-19

Order data for accessories see page 13



Disassembly:



(1) Pull out the filing frame

(2) Detach the pinion retainer clips

Lift latch and pull the clip backwards

(3) Remove the connection rod



(4) Remove the filing frame (see illustration)

Lock rear panel by bending over the latch at the slide panel.

Lift frame at the frontside and pull forward until the bayonet lanchings are released, then take off the frame.





Vertical graduation system 25 mm.



* Regarding cabinets with a front cover, the hole pattern in the side walls has to be adjusted accordingly in case of additional tacks being used to stop the front cover 1-2 mm before the front edge of the cabinet.


Vertical graduation system 32 mm.




* Regarding cabinets with a front cover, the hole pattern in the side walls has to be adjusted accordingly in case of additional tacks being used to stop the front cover 1-2 mm before the front edge of the cabinet.

Minimum dimension with damping system "Soft Control 2": 26 mm

Depth dimensions for installation with front cover.



Depth dimensions for installation behind doors.




Width variations.

Standard Pro-Line II filing frames are configured for single cabinets with 19 mm side walls. However, by inserting spacers they can also be used with row cabinets or even adapted to side walls with 16 mm thickness. This allows the same frame to be used for all cabinet variations.

The spacers are mounted between the cabinet brackets and the cabinet wall. When a locking system is installed, the locking bar is routed between spacer and cabinet bracket.



Cabinet bracket 17 mm
with spacer 9,5 mm





| Cabinet type | | Spacer type | Demand | Article No. | UQ |
|----------------|-------|----------------|-----------|-------------------|---------|
| Row cabinet | 19 mm | Spacer 9,5 mm | 2 pieces | 092.06667H | 20 pcs. |
| Single cabinet | 16 mm | Spacer 3,0 mm | each | 092.06666H | 20 pcs. |
| Row cabinet | 16 mm | Spacer 11,0 mm | side wall | 092.06668H | 20 pcs. |

Locking systems.

The adaptation to a locking system is possible by means of lock-catch plates which will be mounted on the sides of the filing frame. In the shrouds there are holes for installation with a front cover or behind doors (offset 22 mm). The locking bar will be mounted between the cabinet bracket and the side wall.

One locking device is sufficient

Combined with the parallel guidance "Syncro" one single locking device is sufficient. Grace to the double cog rows with involute toothing the blocking force is similar to a locking system.



| Description | Side | Colour | Article No. | UQ |
|--|---------|-------------|-------------------|---------|
| Lock-catch plate Huwil SVS3 | right * | silver grey | 092.06674Z | 20 pcs. |
| Lock-catch plate Lehmann Simultan Stop | right * | silver grey | 092.06675Z | 20 pcs. |
| Lock-catch plate Ojmar Sistema 1038 | right * | silver grey | 092.06676Z | 20 pcs. |
| Lock-catch plate Standard | right * | silver grey | 092.06677H | 10 pcs. |

* Lock-catch plates for the left-hand side available on request


Customized solutions.

Standard Pro-Line II filing frames have shrouds for completely concealing the slides.





The variant with half shrouds offers a space savings of 6 mm per side, e.g. for installation behind doors (2).

The variant with mixed shrouds allows it to achieve the required partition also with reduced interior width, e.g. 3 x A4 in cabinets with horizontal shutters (3).

Variant (4) is an alternative when locking mechanisms are not needed.



Further special solutions, e.g. with integrated blocking device "Tilt-Control" please find in our brochure "Filing frame Basic-Line".



| Cabinet width / Partition | Frame width [mm] | Interior cabinet width | | | |
|---------------------------------|---------------------|------------------------|------|------|------|
| | | (1) | (2) | (3) | (4) |
| Overall cabinet width 600 mm* | 480 | 562 | 562 | - | - |
| Overall cabinet width 800 mm* | 680 | 762 | 762 | - | - |
| Overall cabinet width 1 000 mm* | 880 | 962 | 962 | - | - |
| Overall cabinet width 1 200 mm* | 1080 | 1162 | 1162 | - | - |
| Partition 1 x A4 | 324 | 406 | 406 | 396 | 385 |
| Partition 2 x A4 or 3 x A5 | 676 | 758 | 758 | 748 | 737 |
| Partition 3 x A4 | 1028 | 1110 | 1110 | 1100 | 1089 |

* Basis for interior cabinet width: Single cabinet with 19 mm side walls

Accessories for Pro-Line II filing frame.


Cross bar made of steel

Frame depth: 280 / 330 / 385 / 480 mm
 Colour: black
 incl. 2 plastic retainers
 Order data see page 18




Wire bracket for filing maps

Track width: 330 mm [A4]
 Finish: galvanised
 Order data see page 19



Index-card box made of steel

Frame depth: 330 / 480 mm
 Colour: black
 Order data see chart below




| Description | FD | H | W | WI | Article No. | UQ |
|-----------------------------|-----|-----|-------|-------|-------------------|---------|
| Index-card box A4 crosswise | 330 | 210 | 333,7 | 323,7 | 092.09941H | 1 pce. |
| Index-card box A5 crosswise | 330 | 148 | 222,5 | 212,5 | 092.09943H | 1 pce. |
| Index-card box A6 crosswise | 330 | 105 | 166,9 | 156,9 | 092.09945H | 1 pce. |
| Index-card box A4 crosswise | 480 | 210 | 333,7 | 323,7 | 092.09942H | 1 pce. |
| Index-card box A5 crosswise | 480 | 148 | 222,5 | 212,5 | 092.09944H | 1 pce. |
| Index-card box A6 crosswise | 480 | 105 | 166,9 | 156,9 | 092.09946H | 1 pce. |
| Swivel plate A4 crosswise | | | 333,7 | 323,7 | 092.06658H | 20 pcs. |
| Swivel plate A5 crosswise | | | 222,5 | 212,5 | 092.06660H | 20 pcs. |
| Swivel plate A6 crosswise | | | 166,9 | 156,9 | 092.06662H | 20 pcs. |

Pro-Line II wide drawer.

By assembling a drawer insert, the Pro-Line II filing frame can be converted into an organizable wide drawer. Thanks to its modular construction there are no different parts necessary for filing frames or wide drawers.



Assembly:




(1)-(4) like Pro-Line II filing frame (see page 5)

(5) Remove the edge profiles

from both front panel and rear panel

(6) Install the drawer insert

Fix one border of drawer insert on front panel,
then slightly overbend the drawer insert,
finally fix other border of drawer insert on rear panel.




Order data for basic equipment see page 18-19

Order data for accessories see page 15-17


Accessories for Pro-Line II wide drawer.

Drawer partition for drawer depth 330 mm (A4)




Divider panels and divider plates
made of steel, incl. 2 plastic adapters
Colour: black - UQ: 20 pieces

Divider panel 330 mm - Article No. 092.06669H



Ordering example for partition 3 x A4:


4 pcs. divider panel 092.06669H



Ordering example for partition 6 x A5:

4 pcs. divider panel 092.06669H
3 pcs. divider plate 092.08979H

Divider plate A5 - Article No. 092.08979H




Ordering example for partition 10 x A6:

6 pcs. divider panel 092.06669H
5 pcs. divider plate 092.08528H

Divider plate A6 - Article No. 092.08528H


Accessories for Pro-Line II wide drawer.

Drawer partition for drawer depth 480 mm



Divider panels and divider plates
made of steel, incl. 2 plastic adapters
Colour: black - UQ: 20 pieces

Divider panel 480 mm - Article No. 092.06692H




Divider plate A4
Article No. 092.06688H

Divider plate A5
Article No. 092.06689H

Ordering example for partition 2 x A4 + 2 x A5 + 3 x A6:


4 pcs. divider panel 092.06692H
1 pce. divider plate 092.06688H
4 pcs. divider plate 092.06689H



Alternative partitions


Accessories for Pro-Line II wide drawer.

Index-card formation for drawer depth 330 mm / 480 mm




Divider panels and swivel plates
made of steel, incl. 2 plastic adapters
Colour: black - UQ: 20 pieces

Divider panel 330 mm - Article No. 092.06669H
Divider panel 480 mm - Article No. 092.06692H




Ordering example for formation 2 x A4 crosswise:

Divider panel 330 mm: 3 pcs. 092.06669H
Divider panel 480 mm: 3 pcs. 092.06692H
Swivel plate A4 crosswise: 092.06658H



Ordering example for formation 3 x A5 crosswise:


Divider panel 330 mm: 4 pcs. 092.06669H
Divider panel 480 mm: 4 pcs. 092.06692H
Swivel plate A4 longwise: 092.06659H
Swivel plate A5 crosswise: 092.06660H



Ordering example for formation 4 x A6 crosswise:

Divider panel 330 mm: 5 pcs. 092.06669H
Divider panel 480 mm: 5 pcs. 092.06692H
Swivel plate A5 longwise: 092.06661H
Swivel plate A6 crosswise: 092.06662H

Order data - Basic equipment.



| No. | Description | Frame depth (mm) * | | | | UQ |
|-----|--|--------------------|-------------|-------------------|------------|---------|
| | | 280 | 330 [A4] | 385 [Foolscap] | 480 | |
| 1 | Full extension slide Series 038 premounted assembly with rack, side panel, shroud and 70 mm self-closing device | 055.09490H | 055.09491H | 055.09492H | 055.09493H | 5 sets |
| 2 | Cabinet bracket 4 pieces each filing frame | 053.06650 | 053.06650 | 053.06650 | 053.06650 | 20 pcs. |
| 3 | Cross bar (optional) incl. retainers | 053.09501H | 053.09502H | 053.09503H | 053.09504H | 20 pcs. |

* interior cabinet depth depending on installation (see page 8-9)

| No. | Description | Frame width (mm) / Interior cabinet width (mm) | | | | | UQ |
|-----|---------------------------------------|--|------------|-----------------------|------------|-------------------------|---------|
| | | 324 / 406 [1 x A4] | 480 / 562 | 680 / 762 [2 x A4] | 880 / 962 | 1080 / 1162 [3 x A4] | |
| 4 | Front panel | 053.06950H | 053.06710H | 053.06711H | 053.06917H | 053.06712H | 10 pcs. |
| 5 | Rear panel | 053.09494H | 053.09000H | 053.09001H | 053.09002H | 053.09003H | 10 pcs. |
| 6 | Connection rod premounted assembly | 053.09323H | 053.09341H | 053.09342H | 053.09343H | 053.09344H | 10 pcs. |

| No. | Description | Frame width (mm) / Interior cabinet width (mm) | | | | | UQ |
|-----|---|--|------------|-----------------------|------------|-------------------------|--------|
| | | 324 / 406 [1 x A4] | 480 / 562 | 680 / 762 [2 x A4] | 880 / 962 | 1080 / 1162 [3 x A4] | |
| 7 | Wide drawer insert Drawer depth 330 mm | 092.09820H | 092.09822H | 092.09824H | 092.09826H | 092.09828H | 2 pcs. |
| | Wide drawer insert Drawer depth 480 mm | 092.09821H | 092.09823H | 092.09825H | 092.09827H | 092.09829H | 2 pcs. |

Order data - Accessories.

Installation with front cover:



Installation behind doors:



Mounting the front cover supports

Filing frame:
Insert support pieces from below into the slot of each side panel.

Wide drawer:
Remove edge profiles and screw the support pieces from inside in each side panel with self-tapping screw M3 x 6 mm (Article No. 090.09846).

Mounting the cover caps

The cover caps fix the front panel at the side panels of the filing frame.

Put the cover caps (R/L = right/left) on front panel and front end of shroud; pull the edge profile over both cover caps.

| No. | Description | Finish | Article No. | UQ |
|-----|--|------------|--------------------|----------|
| 7 | Wide drawer insert <i>Dimensions and order data see page 18</i> | black | <i>see page 18</i> | 2 pcs. |
| 8 | Front cover support | black | 092.06651H | 20 pairs |
| 9 | Cover cap | black | 092.06670H | 10 pairs |
| 10 | Wire bracket for filing maps | galvanised | 092.06673Z | 50 pcs. |

We offer our help.



Give us a call or write to us. Together you and your Schock specialist can work out the optimum solution for you.

SCHOCK
M E T A L L

Schock Metallwerk GmbH · Siemensstr. 1-3 · D-73660 Urbach · Tel. +49 7181 808-0 · Fax +49 7181 808-299
E-mail: info@schock-metall.de · Internet: www.schock-metall.de